



Smartphone?!

Just scan our QR code and learn more about our company and our products.



Herding GmbH
FILTERTECHNIK

August-Borsig-Str. 3
92224 Amberg
Germany

Tel.: +49 9621 630-0
Fax: +49 9621 630-120
Mail: info@herding.de

Herding FLEX

HERDING FLEX PRODUCT DESCRIPTION

The flexible filter units series

With the Herding® FLEX series, all proven advantages of pure surface filtration with the Herding® sinter-plate filters are implemented in a compact and space-saving manner. The filter unit series is extremely flexible for volume flows of approx. 500 m³/h up to several 100,000 m³/h.

The filter units of the FLEX-series are equipped with vertically installed sinter-plate filters. Depending on the requirements, Herding® DELTA, DELTA² or HSL filter elements are being used. Unit safety and performance according to the current ATEX-guidelines are coordinated with the unit operator, if required.

The upper part of the filter unit consists either of an integrated fan unit or as a simple housing cover with external fans. The outlet of the clean gas can be designed very flexible, ranging from a simple discharge opening through a discharge grid, to various connection possibilities (flange, beading, smooth) to standardized or individual clean gas ducts.

The Herding sinter-plate filters are the centerpiece in the central part of the filter as well as the interface to the raw gas inlet and the integrated Jet-Pulse cleaning with compressed air supply tank and the integral solenoid valves. All components that are relevant for maintenance are easily accessible from the front side.

The lower end of the unit is formed by the dust discharge. It can be designed individually, according to the particular application and customer requirements. In its simplest form, it consists of a discharge hopper with a dust collecting bin. There are also rotary air lock feeders, screw conveyors, flap systems, pneumatic discharge systems or various customized discharge systems adaptable.



HERDING FLEX PRODUCT FEATURES AND OPTIONS

- » Constant operating conditions by surface filtration
- » Highly efficient cleaning system at a low and energy-saving consumption of compressed air
- » Maintenance doors as displacers with extremely stable stiffening - no escaping of dust
- » Separate valve compartments for the inspection of the dedusting-system during operation
- » Project-specific design of the dust discharge
- » Flow guidance for energy optimization, effective pre-separation and sedimentation
- » Access to all relevant components from the front side
- » Due to the modular design, operating volume flow rates can be up to several 100,000 m³/h
- » Filter media Herding® DELTA, DELTA², HSL are available in non-chargeable or antistatic versions
- » Constructive equipotential bonding of the filter unit
- » Constructive explosion protection by means of pressure relief // explosion suppression
- » Fire protection systems as safeguard
- » Integrated pre-separation systems
- » Herding® MULTICOATER for sticky products
- » Microprocessor control Herding® MP 12 or project-specific control systems
- » Customized discharge systems // fire protection systems // pre-separation systems
- » FirstRinse for the preparation of a filter change free from contamination

APPLICATIONS OF HERDING FLEX SERIES

The Herding FLEX filter unit series is particularly suitable for separation or product recovery of very fine, sticky or abrasive dusts.

PHARMACEUTICAL SOLIDS PRODUCTION

Various filtration requirements arise in the pharmaceutical solids production, e.g. at the tablet forming, granulating, film coating and the general handling of solid drug forms. The robust sinter-plate filters as Dust®Barrier with its extremely low clean gas values, the possibility of the Herding MULTICOATER to even deal with extremely adhesive coating processes, high availability as well as peripheral solutions such as FirstRinse for contamination-free filter change and SafeChange dust discharge, predetermine the FLEX series to be used in pharmaceutical production.



ENAMEL COATING

During the electrostatic enamel-coating, laminar flow conditions and a constant volume flow rate are of vital importance for an ideal and efficient surface coating. In addition, the enamel dusts to be extracted may be highly abrasive. A contamination-free product recovery of the enamel-overspray is possible with the absolutely fiber-free and abrasive-resistant sinter-plate filter elements, because the chance of impurity of the powder is eliminated. The pure surface filtration and the robustness of the rigid body elements are the essential reasons for the use of Herding technology in the enamel industry.



STEEL TUBE PRODUCTION

The production of seamless tubes imposes very high standards on the availability of the overall process including the filter unit.

It is important to ensure that the filter unit continuously sucks away the mixture of steam, metallic oxides and graphite while indenting, shaping and during the rolling process, otherwise the surface quality of the steel tubes decreases due to impurities.



TONER DUSTS

Due to its specific characteristic of non-agglomeration, the production and aspiration of toner powder for colour cartridges sets high requirements on a separator system. Moreover, this involves the ultra-fine dust at the submicron range. A crucial economic factor is the product recovery with the Herding filter system. In the case of constructive explosion protection, the filter unit can be equipped with safety measures such as explosion pressure relief or, alternatively with explosion suppression systems.



Other areas of application for the Herding FLEX series can be found in the following industries:

Automotive, chemicals industry, color pigments, glass industry, plastics, food industry, metal processing, wet paint-dry separation, recycling, solar, nonmetallic minerals, cement, etc.

Our competent sales engineers will be happy to advise you on your individual application!